

[Click to Print This Page](#)



E-VISION LASER 15000 WU DIGITAL PROJECTOR

THE VISIONARIES CHOICE



E-Vision Laser 15000 WU

15,000 ISO / 13,500 ANSI Lumens | Contrast Ratio: 10,000:1 (Dynamic Black) 1,000:1 native | Part Number: 120-995

Key Specifications:

Colour System:	Blue and Red Lasers with Phosphor wheel
Display Type:	1 x 0.67" DarkChip™ DMD™
DMD Specification:	1920 x 1200 pixels native display. Fast transit pixels for smooth greyscale and improved contrast.
Aspect Ratio:	16x10
Fill Factor	87%
Key Features:	<p>Red Laser Assist</p> <ul style="list-style-type: none">• Uses blue and red laser diodes for increased colour fidelity and highly accurate colours <p>Video & Graphics Processing</p> <ul style="list-style-type: none">• HDMI 1.4b for Side by Side, Frame Packing, Frame Sequential & Top Bottom 3D formats.• Dual Flash Processing can be used to multiply the displayed frame rate for 3D sources.• Triple Flash processing for 24Hz 3D input (Frame Packed and Dual Pipe 3D)• Dual Pipe Processing: Two sources in parallel for Left and Right eyes.• Synchronisation of active glasses.• 3GSDI with loop-through.• 24p and 1080p native display.• DICOM simulation mode.

Geometry Correction

- Four Corners, Vertical & Horizontal Keystone, Pincushion & Barrel, Arc and Image Rotation.
- Non Linear Warp.
- Blanking control for custom input window sizing.
- Digital zoom, pan and scan.
- Scaling available for fixed aspect ratio screens and independent input aspect ratios.

Edge Blending

- For independent edge and blend width adjustment.
- Correction for non-active pixels at the edge of the display.
- Electronic black level compensation.

Picture in Picture

- Two sources can be displayed either one within the other (PIP), or side by side, with original aspect ratios maintained.

HDBaseT® Interface

- Built in support for reception of uncompressed High Definition Video over standard CAT5e/6 LAN cable.
- Allows the projector to be placed up to 100m from the source with low cost cabling.

Colour Processing

- Powerful seven point colour correction for accurate colour matching.
- Selectable default colour gamut

Projector Control

- Intuitive user interface for network control

PC Projector Controller Application for:

- Simultaneous control of user-defined groups of projectors
- At-a-glance monitoring of projector status
- Served web pages for browser monitoring and control access from PC's and Smart phones

Projector Automation

- Real-time clock provides daily on/off automation.

Projector Maintenance Features

- Sealed optics.
- Long life 20,000 hour illumination.


Source Compatibility

3GSDI is SMPTE 292M, SMPTE 259M-C and SMPTE 424M compliant.
HDMI including Deep Color™ processing.
Graphics standards up to 1920 x 1200 resolution at 60Hz via HDMI, DisplayPort or VGA.
Component Video (SD and HD) via RGBHV.

Inputs/Outputs

Video & Computer			Communication & Control		
Type	Connector	Qty	Type	Connector	Qty
DVI-D 1.0	DVI	1	3D Sync Out	BNC	1
DisplayPort	DisplayPort	1	3D Sync In	BNC	1
1.1a	HDMI	2	LAN	RJ45	1
HDMI 1.4b	BNC	1	RS232	9-pin D-Sub	1

3G-SDI in	BNC	1	Wired Remote	3.5mm	1
3G-SDI out	15-pin D-	1	12V Trigger	Stereo Jack	2
VGA / Analog	Sub	1	USB Power 5V/2A	3.5mm	1
RGB	15-pin D-	1		Stereo Jack	
VGA Monitor	Sub	1	NOTE: The LAN port is shared with HDBase-T.	USB Type A	
out	5 x BNC		NOTE: USB Power only for WHDI interfaces.		
Component	LAN RJ45				
Video					
HDBaseT (see LAN)					

3D Formats Supported	Frame Packing Dual Pipe Frame Sequential Side By Side (half) Top and Bottom																								
HDTV Formats Supported	1080p (24Hz, 25Hz, 30Hz, 50Hz, 60Hz), 1080i (50Hz, 60Hz), 720p (50, 60Hz)																								
Computer Compatibility	Up to 2560 x 1600 RB displayed within WUXGA																								
Bandwidth	165 MHz on analog RGB 165 Megapixels per second on HDMI																								
Remote Control	Addressable IR remote control, wireless and wired. On-Board keypad.																								
Automation Control	PJLink Class 1 LAN RS-232 AMX (Device Discovery) Served web page Crestron Connected ART-NET control																								
Colour Temperature	3200 to 9300K																								
Operation																									
illumination Type	Blue and Red Laser Light Source																								
Typical illumination Life	20,000 hours																								
Lenses	<table border="1"> <thead> <tr> <th>Lens</th> <th>Part No.</th> <th>Optimised Focus Range*</th> <th>Lens Shift (Frame)</th> </tr> </thead> <tbody> <tr> <td>0.38 :1 fixed</td> <td>117-341</td> <td>0.68m - 2.44m</td> <td>Depends on image size, see Installation Guide.</td> </tr> <tr> <td>0.75 - 0.93 :1 zoom</td> <td>115-339</td> <td>1.02m - 12.7m</td> <td>Vert: 0.5 (U) 0.3 (D) frame, Hor: 0.1(L) 0.2 (R) frame</td> </tr> <tr> <td>0.76 :1 fixed</td> <td>112-499</td> <td>0.81m - 5.08m</td> <td>none</td> </tr> <tr> <td>1.25 - 1.79 :1 zoom</td> <td>112-500</td> <td>1.33m - 11.73m</td> <td>Vert: 0.5 (U) 0.3 (D) frame, Hor: 0.1(L) 0.2 (R) frame</td> </tr> <tr> <td>1.73 - 2.27 :1 zoom</td> <td>112-501</td> <td>1.83m - 14.9m</td> <td>Vert: 0.5 (U) 0.3 (D) frame, Hor: 0.1(L) 0.2</td> </tr> </tbody> </table>	Lens	Part No.	Optimised Focus Range*	Lens Shift (Frame)	0.38 :1 fixed	117-341	0.68m - 2.44m	Depends on image size, see Installation Guide.	0.75 - 0.93 :1 zoom	115-339	1.02m - 12.7m	Vert: 0.5 (U) 0.3 (D) frame, Hor: 0.1(L) 0.2 (R) frame	0.76 :1 fixed	112-499	0.81m - 5.08m	none	1.25 - 1.79 :1 zoom	112-500	1.33m - 11.73m	Vert: 0.5 (U) 0.3 (D) frame, Hor: 0.1(L) 0.2 (R) frame	1.73 - 2.27 :1 zoom	112-501	1.83m - 14.9m	Vert: 0.5 (U) 0.3 (D) frame, Hor: 0.1(L) 0.2
Lens	Part No.	Optimised Focus Range*	Lens Shift (Frame)																						
0.38 :1 fixed	117-341	0.68m - 2.44m	Depends on image size, see Installation Guide.																						
0.75 - 0.93 :1 zoom	115-339	1.02m - 12.7m	Vert: 0.5 (U) 0.3 (D) frame, Hor: 0.1(L) 0.2 (R) frame																						
0.76 :1 fixed	112-499	0.81m - 5.08m	none																						
1.25 - 1.79 :1 zoom	112-500	1.33m - 11.73m	Vert: 0.5 (U) 0.3 (D) frame, Hor: 0.1(L) 0.2 (R) frame																						
1.73 - 2.27 :1 zoom	112-501	1.83m - 14.9m	Vert: 0.5 (U) 0.3 (D) frame, Hor: 0.1(L) 0.2																						

			(R) frame						
	2.22 - 3.67 :1 zoom	112-502	2.36m - 24.2m Vert: 0.5 (U) 0.3 (D) frame, Hor: 0.1(L) 0.2 (R) frame						
	3.58 - 5.38 :1 zoom	112-503	3.8m - 35.35m Vert: 0.5 (U) 0.3 (D) frame, Hor: 0.1(L) 0.2 (R) frame						
	5.31 - 8.26 :1 zoom	112-504	5.59m - 54.8m Vert: 0.5 (U) 0.3 (D) frame, Hor: 0.1(L) 0.2 (R) frame						
	* Lens focal ranges above are the optimised distances but are likely to focus further, please contact your RSM for more details. Lens ratio tolerances: E-Vision Series: +/-3%. HighLite Series: +/- 5%. M-Vision Series: +/- 2%. Titan Series: +/-2%, INSIGHT Series: +/-2%,								
Lens Mount	Motorised and programmable shift, zoom and focus. Intelligent Lens Memory with 10 user-definable preset positions (except UST lens).								
Mechanical Mounting	Front/Rear Table Front/Rear Ceiling Adjustable Front/Rear Feet								
Orientation	Table Top or Inverted: Yes Pointing Up: Yes Pointing Down: Yes Roll (Portrait): Yes								
Power Requirements	200-240VAC 50/60Hz single phase 8.2A 100-130VAC 50/60Hz single phase 11.9A Note: that in 100-130VAC operation, the projector will be at 65% brightness								
Power Consumption	Typical 1570W @ 240VAC in Normal mode Typical 1025W @ 110VAC in Normal mode								
Thermal Dissipation	Typical 5357 BTU/Hour @ 240VAC in Normal mode Typical 3497 BTU/Hour @ 110VAC in Normal mode								
Fan Noise	Normal mode: 48 dBA Max, 46 dBA Typical Eco mode: 45 dBA Max, 43 dBA Typical								
Operating/Storage Temperature Operating:	Operating: 0 to 35C (32 to 95F) Operating: 35 to 40C (95 to 104F) w/ reduced light output Storage: -20 to 60C (-4 to 140F)								
Operating Humidity	10 to 90% relative, non-condensing								
Weight	29.5 kg / 65 lbs								
Dimensions	L: 59.83 cm x W: 50 cm x H: 21.85 cm L: 23.55 in x W: 19.68 in x H: 8.60 in								
Safety & EMC Regulations	UL / cUL, BIS, CB, CCC, KC, FCC (Part 15) Class A, FDA, CE, RoHS 2, IEC EN 60825-1-2014 Class 3R Laser Product, IEC EN 60825-1-2007 Class 1 Laser Product IEC EN 62471-5-2015 Risk Group 3								
Accessories	<table border="1"> <thead> <tr> <th>Accessory</th> <th>Part No.</th> </tr> </thead> <tbody> <tr> <td>Infrared Remote (replacement)</td> <td>117-880</td> </tr> <tr> <td>Lens Hood (Required in the USA for FDA Compliance with lenses 112-503 & 112-504)</td> <td>121-867</td> </tr> </tbody> </table>			Accessory	Part No.	Infrared Remote (replacement)	117-880	Lens Hood (Required in the USA for FDA Compliance with lenses 112-503 & 112-504)	121-867
Accessory	Part No.								
Infrared Remote (replacement)	117-880								
Lens Hood (Required in the USA for FDA Compliance with lenses 112-503 & 112-504)	121-867								

**Dimensions included for reference only and are subject to change. Please download the full set of CAD files for this display for more accurate information.*

Downloads

- [PDF CAD Drawings](#)
- [AUTOCAD Drawings](#)
- [STEP / IGS Drawings](#)
- [Lens CAD Drawings](#)

User Guide

- [User Guides](#)
- [User Guides \(German\)](#)
- [User Guides \(French\)](#)
- [Laser Risk Group Document](#)
- [Important Information](#)
- [Important Information \(German\)](#)
- [Important Information \(French\)](#)
- [Control Protocol](#)
- [Ultra Short Throw Lens](#)
- [Ultra Short Throw Lens Installation Guide](#)



DIGITAL PROJECTION, INC



55 Chastain Road, Suite 115 Kennesaw, GA.

30144



T: 770.420.1350 | F: 770.420.1360



www.digitalprojection.com



DIGITAL PROJECTION, LTD



Greenside Way, Middleton Manchester, UK

M24 1XX



T: +44.161.947.3300 | F: +44.161.684.7674



www.digitalprojection.co.uk



DIGITAL PROJECTION, INC



A Delta Group Company

Specifications subject to change without notice.
©2022 Digital Projection. DLP®, Digital Light Processing™ and DMD are trademarks of Texas Instruments, Inc



Certificate Number 13629
ISO 9001



55 Chastain Road, Suite 115 Kennesaw, GA.

30144



T: 770.420.1350 | F: 770.420.1360



www.digitalprojection.com



DIGITAL PROJECTION, CHINA



Rm A2301, Shaoyaoju 101 North Lane, Shi Ao

International Center, Chaoyang District, Beijing 100029,
PR China



T: +86.10.58239771 | F: +86 10 58239770